

Run Length Chart for 19, 25mm DripMaxx® ND, AS and Maxxi PC drip tube

Diam/Flow	Inlet Pressure kPa	Emitter Spacing							
		0.3m	0.4m	0.5m	0.6m	0.75m	0.9m	1.0m	1.5m
19/1.2									
	200	251	307	358	406	472	534	572	751
	250	289	354	413	468	544	615	660	864
	300	319	391	456	517	601	680	730	956
	350	345	423	493	559	651	735	789	1034
19/1.6									
	200	181	227	270	310	366	418	451	599
	250	208	261	311	356	421	481	518	691
	300	229	288	343	394	465	531	573	764
	350	247	311	370	426	502	574	619	826
25/1.2									
	200	407	496	578	654	759	858	920	1203
	250	468	572	666	753	875	988	1060	1386
	300	518	632	736	833	968	1094	1173	1534
	350	560	683	796	901	1046	1182	1268	1658
25/1.6									
	200	337	411	479	542	630	711	763	998
	250	388	474	552	625	726	820	879	1150
	300	429	524	610	691	803	906	973	1272
	350	464	566	660	747	868	980	1051	1376

Run Lengths are based on flat ground, single lateral runs and maintaining a minimum of 100 kPa in the tube. Do not exceed 350 kPa. Also ensure that the operating pressure does not exceed the pressure rating of the drip tube (dependent on wall thickness)

