

22 mm Aqua-Traxx® Flow Rate Data			
Code	Outlet Spacing (mm)	Average Individual Emitter @ 55 kPa over 100m (L/h)	Flow per 100m @ 55 kPa (L/h)
Low Flow 0.49 L/h @ 55 kPa			
EA7xx0834	200	0.50	284
EA7xx1222	300	0.51	166
EA7xx1617	400	0.51	125
EA7xx2411	600	0.51	83
Medium Flow 0.76 L/h @ 55 kPa			
EA7xx0850	200	0.75	370
EA7xx1234	300	0.76	248
EA7xx1625	400	0.76	187
EA7xx2417	600	0.76	125
Standard Flow 1.02 L/h @ 55 kPa			
EA7xx0867	200	1.00	490
EA7xx1245	300	1.01	329
EA7xx1634	400	1.01	248
EA7xx2422	600	1.01	166
Cane Flow 1.20 L/h @ 55 kPa			
EA7xx0884	200	1.23	606
EA7xx1256	300	1.25	410
EA7xx1642	400	1.26	310
EA7xx2428	600	1.26	207
Emitter flow rate based on average over 100 metres			